



PRODUCT DESCRIPTION

A traditional lantern design uses a two-tone Satin Nickel and Satin Brass metal work create modern coastal flair. The sloping cone in metal supports a rounded Satin White glass diffuser to softly diffuse the light. Choose from two different sizes to use over a kitchen island or as an entry pendant in traditional or transitional settings.

MEASUREMENTS

DIMENSION : 12" L x 12" W x 17.5" H
 MAX OAH : 56.75" OAH
 CANOPY : 5" W x 2" H x 5" L
 HANGING WEIGHT : 7.28 lb

LAMPING

INPUT VOLTAGE : 120V
 BULB : 1 x 60W Incandescent E26 Medium , 60W Total
 BULB INCLUDED : (Not Included)
 DIMMABLE : Y

FINISHES OPTION

 Satin Nickel / Satin Brass

GLASS

White WT

MATERIAL

Steel, Glass

RATINGS

Dry Location



ADDITIONAL

OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746
 EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269
 P. 626.956.4200 | F. 626.956.4225 | maximlighting.com