



**PRODUCT DESCRIPTION**

A traditional lantern design uses a two-tone Satin Nickel and Satin Brass metal work create modern coastal flair. The sloping cone in metal supports a rounded Satin White glass diffuser to softly diffuse the light. Choose from two different sizes to use over a kitchen island or as an entry pendant in traditional or transitional settings.

**MEASUREMENTS**

DIMENSION : 15" L x 15" W x 21.5" H  
 MAX OAH : 60.75" OAH  
 CANOPY : 5.5" W x 2.25" H x 5.5" L  
 HANGING WEIGHT : 10.69 lb

**LAMPING**

INPUT VOLTAGE : 120V  
 BULB : 1 x 60W Incandescent E26 Medium , 60W Total  
 BULB INCLUDED : (Not Included)  
 DIMMABLE : Y

**FINISHES OPTION**

 Satin Nickel / Satin Brass

**GLASS**

White WT

**MATERIAL**

Steel, Glass

**RATINGS**

Dry Location



**ADDITIONAL**

OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER  
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com