



**PRODUCT DESCRIPTION**

A sizable layered glass oscillates depth and is supported by three industrial set screws for support. Available as a pendant or flush mount, the pendant also features an oversized ring to evoking nautical vibes while remaining minimalist in its design. Available in Satin Brass, Satin Nickel, or Matte Black, pair the clear glass shades with a vintage filament lamps to complete the look.

**MEASUREMENTS**

DIMENSION : 12" W x 15.25" H  
 MAX OAH : 57" OAH  
 CANOPY : 5" W x 0.75" H x 5" L  
 HANGING WEIGHT : 4.4 lb

**LAMPING**

INPUT VOLTAGE : 120V  
 BULB : 1 x 60W Incandescent E26 Medium , 60W Total  
 BULB INCLUDED : (Not Included)  
 DIMMABLE : Y

**FINISHES OPTION**

-  Black
-  Satin Brass
-  Satin Nickel

**GLASS**

Clear CL

**MATERIAL**

Steel + Glass

**RATINGS**

cULus  
 Dry Location



**ADDITIONAL**

OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER  
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com