



**PRODUCT DESCRIPTION**


A minimalist design featuring a metal frame of Black round glass balls in your choice of Mirror Smoke for a contemporary style or Champagne for more transitional decors. The value of this collection is increased by the inclusion of LED bulbs.

**MEASUREMENTS**

DIMENSION : 9.75" L x 9.75" W x 14.5" H  
 CANOPY : 9.75" W x 0.5" H x 9.75" L  
 HANGING WEIGHT : 4.89 lb

**LAMPING**

INPUT VOLTAGE : 120V  
 LUMENS : 500 Rated (450 Del.)  
 BULB : 1 x 4W LED G9 , 4W Total  
 BULB INCLUDED : (Included)  
 DIMMABLE : Triac CL  
 COLOR\_TEMP : 3000K



**FINISHES OPTION**

- Black / Polished Chrome
- Black / Satin Brass

**GLASS**

Mirror Smoke MSK

**MATERIAL**

Steel, Glass

**RATINGS**

cETLus  
 Dry Location



**ADDITIONAL**

RATED LIFE 15000 Hours  
 OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER  
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com