



**PRODUCT DESCRIPTION**

A minimalist design featuring a metal frame of Black round glass balls in your choice of Mirror Smoke for a contemporary style or Champagne for more transitional decors. The value of this collection is increased by the inclusion of LED bulbs.

**MEASUREMENTS**

DIMENSION : 15" L x 15" W x 17.75" H  
 MAX OAH : 63.75" OAH  
 CANOPY : 4.75" W x 0.75" H x 4.75" L  
 HANGING WEIGHT : 9.78 lb

**LAMPING**

INPUT VOLTAGE : 120V  
 LUMENS : 600 Rated  
 BULB : 1 x 6W LED E26 Medium , 6W Total  
 BULB INCLUDED : (Included)  
 DIMMABLE : Triac CL  
 COLOR\_TEMP : 3000K

**FINISHES OPTION**

-  Black / Polished Chrome
-  Black / Satin Brass

**GLASS**

Mirror Smoke MSK

**MATERIAL**

Steel, Glass

**RATINGS**

cULus  
 Dry Location



**ADDITIONAL**

ADJUSTABLE  
 SLOPE: 90  
 RATED LIFE NA Hours  
 OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER  
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maxilighting.com