



PRODUCT DESCRIPTION

Clear glass cylinders lined with mesh screen are supported by knurled cups of Polished Chrome creates a contemporary design with an industrial twist. This economical collection provides a designer

MEASUREMENTS

DIMENSION : 11.5" L 10.5" H x 6.5" Ext
BACK PLATE : 6" W x 4.5" H x 2.25" HCO
HANGING WEIGHT : 3.02 lb

LAMPING

INPUT VOLTAGE : 120V
BULB : 2 x 60W Incandescent E26 Medium , 120W Total
BULB INCLUDED : (Not Included)
DIMMABLE : Yes
LIGHTING_DIRECTION : Up/Down

FINISHES OPTION

 Polished Chrome

GLASS

Clear CL

MATERIAL

Steel, Glass

RATINGS

cULus
Damp Location



ADDITIONAL

INSTALL UP/DOWN: Up/Down
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com