



**PRODUCT DESCRIPTION**

Clear glass cylinders lined with mesh screen are supported by knurled cups of Polished Chrome creates a contemporary design with an industrial twist. This economical collection provides a designer

**MEASUREMENTS**

DIMENSION : 19" L 10.5" H x 6.5" Ext  
 BACK PLATE : 6" W x 4.5" H x 2.25" HCO  
 HANGING WEIGHT : 4.19 lb

**LAMPING**

INPUT VOLTAGE : 120V  
 BULB : 3 x 60W Incandescent E26 Medium , 180W Total  
 BULB INCLUDED : (Not Included)  
 DIMMABLE : Yes  
 LIGHTING\_DIRECTION : Up/Down

**FINISHES OPTION**

 Polished Chrome

**GLASS**

Clear CL

**MATERIAL**

Steel, Glass

**RATINGS**

cULus  
 Damp Location



**ADDITIONAL**

INSTALL UP/DOWN: Up/Down  
 OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER  
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maxilighting.com