



PRODUCT DESCRIPTION

Clear glass cylinders lined with mesh screen are supported by knurled cups of Polished Chrome creates a contemporary design with an industrial twist. This economical collection provides a designer

MEASUREMENTS

DIMENSION : 26" L 10.5" H x 6.5" Ext
 MAX OAH : 6" W x 4.5" H
 HANGING WEIGHT : 5.34 lb

LAMPING

INPUT VOLTAGE : 120V
 BULB : 4 x 60W Incandescent E26 Medium , 240W Total
 BULB INCLUDED : (Not Included)
 DIMMABLE : Yes
 LIGHTING_DIRECTION : Up/Down

FINISHES OPTION

 Polished Chrome

GLASS

Clear CL

MATERIAL

Steel, Glass

RATINGS

cULus
 Damp Location



ADDITIONAL

INSTALL UP/DOWN: Up/Down
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com