



PRODUCT DESCRIPTION

Sockets are suspended above a metal spun dome in your choice of Black or White with Gold accents or Satin Nickel with Black accents. A clean and simple approach to modern or transitional lighting, the opening allows light to shine through the opening atop while providing functional light below. This break in the two parts is supported with straps and decorative rivets in complimentary finishes for a subtly tasteful two-tone finish. A coordinating pin-up wall sconce offers a bedside application to this design with integrated switch on its back plate and two feet of cord cover that can be removed and hardwired per your preference.

MEASUREMENTS

DIMENSION : 7" W x 12.5" H x 11" Ext
MAX OAH : 5.5" W x 5.5" H
HANGING WEIGHT : 2.07 lb

LAMPING

INPUT VOLTAGE : 120V
BULB : 1 x 60W Incandescent E26 Medium , 60W Total
BULB INCLUDED : (Not Included)
LIGHTING_DIRECTION : Directional

FINISHES OPTION

 Antique Brass / Black
 Satin Nickel
 White/Satin Brass

MATERIAL

Steel, Aluminum

RATINGS

Dry Location

ADDITIONAL

INSTALL UP/DOWN: Up
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.