

**PRODUCT DESCRIPTION**

Understated elegance and convenience in its design, the simple curved arms of the Bristol collection outstretch in elongated proportions that terminate at a tapered Satin White glass shade. Designed to emulate a traditional fabric shade, the material being glass adds the element of easy maintenance and allows for upward and downward facing light installations. The single tiered wider diameters on the chandeliers also offer an upscale country living addition to the collection. Available in various finishes of Satin Nickel, Satin Brass, or black tones including a textured Anthracite finish on the chandeliers and sconces.

MEASUREMENTS

DIMENSION : 13.25" W x 10" H x 6" Ext

MAX OAH : 4.75" W x 4.75" H


HANGING WEIGHT : 2.65 lb

LAMPING

INPUT VOLTAGE : 120V

BULB : 2 x 60W Incandescent E26 Medium , 120W Total

BULB INCLUDED : (Not Included)

FINISHES OPTION**GLASS**

Satin White SW

MATERIAL

Steel, Glass

RATINGS

Damp Location

**ADDITIONAL**

INSTALL UP/DOWN: Up/Down

OPERATING TEMPERATURE:

-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com