



PRODUCT DESCRIPTION

Pure White plaster sloping cones are hung on chains connected to a modern yoke structure finished in your choice of Aged Brass or Matte Black. The charming earthiness of the plaster is juxtaposed by the modern, angular hanging structure with Scandinavian influence in its form making this collection folksy and refreshing.

MEASUREMENTS

DIMENSION : 13" L x 13" W x 15" H
 MAX OAH : 95" OAH
 CANOPY : 5" W x 0.5" H x 5" L
 HANGING WEIGHT : 15.4 lb

LAMPING

INPUT VOLTAGE : 120V
 BULB : 1 x 40W Incandescent E26 Medium , 40W Total
 BULB INCLUDED : (Not Included)
 DIMMABLE : Y

FINISHES OPTION

 Black
 Satin Brass

GLASS

White WT

MATERIAL

Plaster, Steel

RATINGS

cETLus
 Dry Location
 JA8 Bulb In



ADDITIONAL

OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com