



#### PRODUCT DESCRIPTION

Internally ribbed clear glass tubes refract tubular lamps, creating a shimmering light effect. The glass is supported by a two-tone black frame with Aged Brass accents, making this sconce suitable for both indoor and outdoor installations. With a depth of less than 4 inches, this ADA compliant sconce may also be used in commercial applications.

#### MEASUREMENTS

DIMENSION : 5" W x 11" H x 4" Ext  
 BACK PLATE : 4.7" W x 9.75" H x 5.5" HCO  
 HANGING WEIGHT : 2.56 lb

#### LAMPING

INPUT VOLTAGE : 120V  
 BULB : 1 x 60W Incandescent E26 Medium , 60W Total  
 BULB INCLUDED : (Not Included)  
 DIMMABLE : Y

#### FINISHES OPTION

 Black / Antique Brass

#### GLASS

Clear Ribbed CR

#### MATERIAL

Aluminum

#### RATINGS

cETLus  
 Wet Location  
 ADA



#### ADDITIONAL

INSTALL UP/DOWN: Up  
 OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.