



PRODUCT DESCRIPTION

Internally ribbed clear glass tubes refract tubular lamps, creating a shimmering light effect. The glass is supported by a two-tone black frame with Aged Brass accents, making this sconce suitable for both indoor and outdoor installations. With a depth of less than 4 inches, this ADA compliant sconce may also be used in commercial applications.

MEASUREMENTS

DIMENSION : 5" W x 14" H x 4" Ext
 BACK PLATE : 4.7" W x 12.75" H x 7" HCO
 HANGING WEIGHT : 3 lb

LAMPING

INPUT VOLTAGE : 120V
 BULB : 2 x 60W Incandescent E26 Medium , 120W Total
 BULB INCLUDED : (Not Included)
 DIMMABLE : Y

FINISHES OPTION

 Black / Antique Brass

GLASS

Clear Ribbed CR

MATERIAL

Aluminum

RATINGS

cETLus
 Wet Location
 ADA



ADDITIONAL

INSTALL UP/DOWN: Up
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.