



PRODUCT DESCRIPTION

A modern tribute to the wheel chandelier, the Ovation collection integrates LED technology for a dazzling lighting effect. The LED light produces a shimmering lighting effect along the tall and narrow fluted glass shades adding celebratory effervescence. The expansive diameters of the rings join at the center in equipoise using four down rods to suspend the frame. Mount the chandelier from the collector or make use of additional chain supplied to extend the height with ease. Additional sconces with up and down lighting complete the design. Available in Brushed Brass or Black, the collection toasts a classic design creating an elegant statement.

MEASUREMENTS

DIMENSION : 23.5" L x 23.5" W x 26.5" H
 MAX OAH : 68" OAH
 CANOPY : 4.75" W x 0.5" H x 4.75" L
 HANGING WEIGHT : 13.25 lb

LAMPING

INPUT VOLTAGE : 120V
 LUMENS : 1,260 Rated (900 Del.)
 BULB : 9 x 2W LED DC Integrated , 18W Total
 BULB INCLUDED : (Integrated)
 DIMMABLE : Triac / 0-10V
 CRI : 80 CRI
 COLOR_TEMP : 3000K

FINISHES OPTION

 Black
 Gold

GLASS

Clear Ribbed CR

MATERIAL

Steel, Ribbed Glass

RATINGS

Dry Location



ADDITIONAL

OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com