



#### PRODUCT DESCRIPTION

A modern tribute to the wheel chandelier, the Ovation collection integrates LED technology for a dazzling lighting effect. The LED light produces a shimmering lighting effect along the tall and narrow fluted glass shades adding celebratory effervescence. The expansive diameters of the rings join at the center in equipoise using four down rods to suspend the frame. Mount the chandelier from the collector or make use of additional chain supplied to extend the height with ease. Additional sconces with up and down lighting complete the design. Available in Brushed Brass or Black, the collection toasts a classic design creating an elegant statement.

#### MEASUREMENTS

DIMENSION : 31.5" L x 31.5" W x 24.35" H  
 MAX OAH : 65.5" OAH  
 CANOPY : 5.75" W x 1.5" H x 5.75" L  
 HANGING WEIGHT : 16.28 lb

#### LAMPING

INPUT VOLTAGE : 120V  
 LUMENS : 2,520 Rated (1,620 Del.)  
 BULB : 12 x 3W LED PCB Integrated , 36W Total  
 BULB INCLUDED : (Integrated)  
 DIMMABLE : Triac / 0-10V  
 CRI : 80 CRI  
 COLOR\_TEMP : 3000K

#### FINISHES OPTION



#### GLASS

Clear Ribbed CR

#### MATERIAL

Aluminum, Steel, Glass

#### RATINGS

cETLus  
 Dry Location



#### ADDITIONAL

RATED LIFE 50000 Hours  
 OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER  
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maxilighting.com