



PRODUCT DESCRIPTION

This series draws inspiration from regal agrarian manors, delivering a statement in its scale and sophisticated finishes. Designed in operatic proportions, the bottom chandelier assembly features swollen curves hand painted in a choice of Ecu White or Golden Noir and suspended by a rigid hook structure replete with vintage charm. These finish combinations not only add dimension and interest, but they are enhanced with the contrastingly brighter accents against the rich, weathered finishes. Extended chain links with smoky beveled crystal charms drape the Ecu and Gold Leaf finish combination, while the darker Golden Noir variation features strands of patinaed silver wooden beads.

MEASUREMENTS

DIMENSION : 32" L x 32" W x 43" H
 MAX OAH : 83.25" OAH
 CANOPY : 5" W x 1.18" H x 5" L
 HANGING WEIGHT : 11.22 lb

LAMPING

INPUT VOLTAGE : 120V
 BULB : 8 x 60W Incandescent E12 Candelabra , 480W Total
 BULB INCLUDED : (Not Included)
 DIMMABLE : Y

FINISHES OPTION

 Ecu/Venetian Gold
 Golden Noir

MATERIAL

Steel, Glass

RATINGS

cETLus
 Dry Location



ADDITIONAL

OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com