



PRODUCT DESCRIPTION

Satin White glass globes are nested behind rings of Gold which dramatically contrasts against the Black metal background. Soft and natural light is provided by replaceable G9 LED lamps which are included in each fixture.

MEASUREMENTS

DIMENSION : 27.25" L 5.5" H x 6.25" Ext
BACK PLATE : 27" W x 4.75" H x 3" HCO
HANGING WEIGHT : 6.16 lb

LAMPING

INPUT VOLTAGE : 120V
LUMENS : 2,000 Rated (1,800 Del.)
BULB : 4 x 4W LED G9 , 16W Total
BULB INCLUDED : (Included)
DIMMABLE : Triac CL
CRI : 80 CRI
COLOR_TEMP : 3000K
LIGHTING_DIRECTION : Up/Down

FINISHES OPTION

 Black / Gold

GLASS

Satin White SW

MATERIAL

Steel, Glass

RATINGS

cETLus
Damp Location



ADDITIONAL

INSTALL UP/DOWN: Up/Down
RATED LIFE 20000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
4200 SHIRLEY DR. | ATLANTA, GA 30336

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com