



PRODUCT DESCRIPTION

A modern take on the classic torchiere, the bright Satin Brass frames support thick textured glass cauldrons illuminated with dedicated LED modules. The 2-Light pendant and swing arm pin-up sconce feature rotatable shades directing the light either upward or cast directionally downward. The deep pattern in the glass sparks curiosity and fascination with its organic and abstract surface. It creates interest in the LED light source behind it while casting even light through the artistic vessels' design. Available in various configurations of pendants and sconces, the collection celebrates classic design concepts in an understated contemporary glamor that results in a composition suited to transitional and contemporary aesthetics. Make a statement with the oversized with the 3-light sconce nearly five foot in height or use the multiple functional pieces for reading over an island.

MEASUREMENTS

DIMENSION	: 10" L x 10" W x 13.75" H
MAX OAH	: 135.25" OAH
CANOPY	: 4.75" W x 1.5" H x 4.75" L
HANGING WEIGHT	: 4.62 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 450 Rated (290 Del.)
BULB	: 1 x 6W LED DC Integrated , 6W Total
BULB INCLUDED	: (Integrated)
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Directional

FINISHES OPTION



Satin Brass

GLASS

Textured Clear TC

MATERIAL

Steel, Stylized Glass

RATINGS

Damp Location



ADDITIONAL

OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com