




PRODUCT DESCRIPTION

This collection of forever classic designs are available in both Satin Nickle and Black finishes with Clear glass. These fixtures were designed to install easily and priced to work in builder packages.



*Height from center of outlet to the top of the fixture

MEASUREMENTS

- DIMENSION : 21.25" L 8" H x 6" Ext
- BACK PLATE : 4.75" W x 4.75" H x 6" HCO
- HANGING WEIGHT : 3.13 lb

LAMPING

- INPUT VOLTAGE : 120V
- BULB : 3 x 60W Incandescent E12 Candelabra , 180W Total
- BULB INCLUDED : (Not Included)
- DIMMABLE : Yes
- LIGHTING_DIRECTION : Up

FINISHES OPTION

- Black
- Satin Nickel

GLASS

Clear CL

MATERIAL

Steel, Glass

RATINGS

cULus
Damp Location



ADDITIONAL

INSTALL UP/DOWN: Up
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746
EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269
P. 626.956.4200 | F. 626.956.4225 | maximlighting.com