




**PRODUCT DESCRIPTION**

This collection of forever classic designs are available in both Satin Nickle and Black finishes with Clear glass. These fixtures were designed to install easily and priced to work in builder packages.



\*Height from center of outlet to the top of the fixture

**MEASUREMENTS**

- DIMENSION : 30" L 8" H x 6" Ext
- BACK PLATE : 4.75" W x 4.75" H x 6" HCO
- HANGING WEIGHT : 4.03 lb

**LAMPING**

- INPUT VOLTAGE : 120V
- BULB : 4 x 60W Incandescent E12 Candelabra , 240W Total
- BULB INCLUDED : (Not Included)
- DIMMABLE : Yes
- LIGHTING\_DIRECTION : Up

**FINISHES OPTION**

- Black
- Satin Nickel

**GLASS**

Clear CL

**MATERIAL**

Steel, Glass

**RATINGS**

cULus  
Damp Location



**ADDITIONAL**

INSTALL UP/DOWN: Up  
OPERATING TEMPERATURE:  
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER  
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com