

**PRODUCT DESCRIPTION**

Two tone frames of Black or White with internal Gold frames provides a neoclassical approach to the squared coach lantern. The sconces jut out from the wall on well-defined trusses that add a contemporary element. Delivering classic design that suits most exteriors, this collection adds interest in the interior contrasting frame of Gold that secures clear glass panes to diffuse the lamp within.

MEASUREMENTS

DIMENSION : 7" W x 12.5" H
MAX OAH : 57.5" OAH
HANGING WEIGHT : 2.75 lb

LAMPING

INPUT VOLTAGE : 120V
BULB : 1 x 60W Incandescent E26 Medium , 60W Total
BULB INCLUDED : (Not Included)
DIMMABLE : Y

FINISHES OPTION

 Black / Gold
 White/Gold

GLASS

Clear CL

MATERIAL

Aluminum, Glass

RATINGS

Wet Location

**ADDITIONAL**

OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com