



PRODUCT DESCRIPTION

Two tone frames of Black or White with internal Gold frames provides a neoclassical approach to the squared coach lantern. The sconces jut out from the wall on well-defined trusses that add a contemporary element. Delivering classic design that suits most exteriors, this collection adds interest in the interior contrasting frame of Gold that secures clear glass panes to diffuse the lamp within.

FINISHES OPTION



GLASS

Clear CL

MATERIAL

Aluminum, Glass


RATINGS

cETLus
Wet Location



ADDITIONAL

INSTALL UP/DOWN: Down
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)



MEASUREMENTS

DIMENSION : 12" W x 29" H x 14" Ext
BACK PLATE : 5.5" W x 12.5" H x 5" HCO
HANGING WEIGHT : 19.14 lb

LAMPING

INPUT VOLTAGE : 120V
BULB : 4 x 40W Incandescent E12 Candelabra , 160W Total
BULB INCLUDED : (Not Included)

*Height from center of outlet to the top of the fixture

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com