



#### PRODUCT DESCRIPTION

An impactful shrine of light, the modern lantern designs of the Pagoda series feature a stacked structure with slanted roof lines over an open pavilion free of glass. The LED light source is contained in the lower structure provides ample light downwards in addition to casting light upwards to create a warm glow within the frame. A large, flattened ring perches above the lanterns, which are then supported by hooks on the larger sizes. The fixtures are made more robust by eliminating the use of glass panels entirely. Finished in matte Black, these outdoor sconces are stylishly contemporary.

#### MEASUREMENTS

DIMENSION : 7.5" W x 15.5" H x 8.5" Ext  
 BACK PLATE : 4.5" W x 6.5" H x 4.25" HCO  
 HANGING WEIGHT : 2 lb

#### LAMPING

INPUT VOLTAGE : 120V  
 LUMENS : 910 Rated (450 Del.)  
 BULB : 2 x 6W LED AC Integrated , 12W Total  
 BULB INCLUDED : (Integrated)  
 DIMMABLE : Y  
 CRI : 90 CRI  
 COLOR\_TEMP : 3000K  
 LIGHTING\_DIRECTION : Up/Down

#### FINISHES OPTION

 Black

#### MATERIAL

Aluminum

#### RATINGS

cETLus  
 Wet Location



#### ADDITIONAL

INSTALL UP/DOWN: Down  
 RATED LIFE 35000 Hours  
 OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER  
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com