

**PRODUCT DESCRIPTION**

An impactful shrine of light, the modern lantern designs of the Pagoda series feature a stacked structure with slanted roof lines over an open pavilion free of glass. The LED light source is contained in the lower structure provides ample light downwards in addition to casting light upwards to create a warm glow within the frame. A large, flattened ring perches above the lanterns, which are then supported by hooks on the larger sizes. The fixtures are made more robust by eliminating the use of glass panels entirely. Finished in matte Black, these outdoor sconces are stylishly contemporary.

MEASUREMENTS

DIMENSION : 9" W x 18.5" H x 10" Ext
BACK PLATE : 4.5" W x 7.75" H x 5" HCO
HANGING WEIGHT : 3.4 lb

LAMPING

INPUT VOLTAGE : 120V
LUMENS : 1,190 Rated (750 Del.)
BULB : 2 x 9W LED AC Integrated , 18W Total
BULB INCLUDED : (Integrated)
DIMMABLE : Y
CRI : 90 CRI
COLOR_TEMP : 3000K
LIGHTING_DIRECTION : Up/Down

FINISHES OPTION

 Black

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location

**ADDITIONAL**

INSTALL UP/DOWN: Down
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com