



PRODUCT DESCRIPTION

The Manchester series is inspired by classic coach lanterns and consists of minimally extended sconces in a variety of sizes that have been modified with simplified embellishments. The black frames have been modified with a squared arc handle and a contrasting Burnished Gold plate that reflects clusters of candle lights surrounded by Clear glass panels. This collection references historic exterior sconces while modernizing their appearance. Complement the design with tubular lamps to accentuate the verticality of the frames.

MEASUREMENTS

DIMENSION : 9" W x 14" H x 5.5" Ext
 BACK PLATE : 4.5" W x 6.75" H x 8.5" HCO
 HANGING WEIGHT : 4 lb

LAMPING

INPUT VOLTAGE : 120V
 BULB : 1 x 60W Incandescent E26 Medium , 60W Total
 BULB INCLUDED : (Not Included)
 DIMMABLE : Y

FINISHES OPTION

 Black

GLASS

Clear CL

MATERIAL

Aluminum, Glass

RATINGS

cETLus
 Wet Location



ADDITIONAL

INSTALL UP/DOWN: Up
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com