



**PRODUCT DESCRIPTION**

The Manchester series is inspired by classic coach lanterns and consists of minimally extended sconces in a variety of sizes that have been modified with simplified embellishments. The black frames have been modified with a squared arc handle and a contrasting Burnished Gold plate that reflects clusters of candle lights surrounded by Clear glass panels. This collection references a historic exterior sconces while modernizing their appearance. Complement the design with tubular lamps to accentuate the verticality of the frames.

**MEASUREMENTS**

DIMENSION : 11.5" W x 30" H x 5.5" Ext  
 BACK PLATE : 5" W x 9.25" H x 17" HCO  
 HANGING WEIGHT : 9.5 lb

**LAMPING**

INPUT VOLTAGE : 120V  
 BULB : 3 x 60W Incandescent E12 Candelabra , 180W Total  
 BULB INCLUDED : (Not Included)  
 DIMMABLE : Y

**FINISHES OPTION**

 Black

**GLASS**

Clear CL

**MATERIAL**

Aluminum, Glass

**RATINGS**

cETLus  
 Wet Location



**ADDITIONAL**

INSTALL UP/DOWN: Up  
 OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746  
 EASTERN DISTRIBUTION CENTER  
 101 GARDNER PARK | PEACHTREE CITY, GA 30269  
 P. 626.956.4200 | F. 626.956.4225 | maximlighting.com