



PRODUCT DESCRIPTION

The conical metal shades on these outdoor sconces draw inspiration from the heartland using embellishments such as riveted accents and fastened rings to add rustic charm. The products are finished in a rich Bronze outdoor rated powder coat, and complements similarly styled exterior elements such as honed stone facades and wood siding.

MEASUREMENTS

DIMENSION : 10.25" W x 14.5" H x 11.75" Ext
 BACK PLATE : 4.75" W x 5.75" H x 7.75" HCO
 HANGING WEIGHT :

LAMPING

INPUT VOLTAGE : 120V
 BULB : 1 x 60W Incandescent E26 Medium , 60W Total
 BULB INCLUDED : (Not Included)
 DIMMABLE : Y
 LIGHTING_DIRECTION : Down

FINISHES OPTION

 Oriental Bronze

MATERIAL

Aluminum

RATINGS

Wet Location
 DARKSKY



ADDITIONAL

INSTALL UP/DOWN: Down
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com