


## PRODUCT DESCRIPTION

Rectangular Beveled Crystals are suspended from a channel of Polished Chrome. The crystal sparkles and shimmers when illuminated by the LED source encased in the channel. This contemporary will add elegance to a wide variety of room decors.



## MEASUREMENTS

DIMENSION : 35.25" L x 5.5" W x 4.25" H x 5.5" Ext  
BACK PLATE : 35.25" W x 4.75" H x 2.25" HCO  
HANGING WEIGHT : 7.05 lb

## LAMPING

INPUT VOLTAGE : 120V  
LUMENS : 1,330 Rated (950 Del.)  
BULB : 1 x 19W LED PCB Integrated , 19W Total  
BULB INCLUDED : (Integrated)  
DIMMABLE : Triac CL  
CRI : 80+ CRI  
COLOR\_TEMP : 3000K  
LIGHTING\_DIRECTION : Down

## FINISHES OPTION

 Polished Chrome

## GLASS

Beveled Crystal BC

## MATERIAL

Steel, Stainless Steel, Crystal

## RATINGS

cETLus  
Damp Location



## ADDITIONAL

INSTALL UP/DOWN: Down  
RATED LIFE 25000 Hours  
OPERATING TEMPERATURE:  
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



**WESTERN DISTRIBUTION CENTER (HEADQUARTER)**  
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

**EASTERN DISTRIBUTION CENTER**  
4200 SHIRLEY DR. | ATLANTA, GA 30336

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com