



**PRODUCT DESCRIPTION**


Stately outdoor sconces reference classic lantern shapes and are constructed of Maxim's proprietary Vivex composite, a robust weather-resistant materials guaranteed to withstand harsh weather climates. Available in several sizes and illuminated with clusters of candle sockets, this is a timeless design built to last.

**MEASUREMENTS**

DIMENSION : 10" W x 24.25" H  
 HANGING WEIGHT : 6.89 lb

**LAMPING**

INPUT VOLTAGE : 120V  
 BULB : 2 x 40W Incandescent E12 Candelabra , 80W Total  
 BULB INCLUDED : (Not Included)  
 DIMMABLE : Y



**FINISHES OPTION**

 Black

**GLASS**

Clear CL

**MATERIAL**

EPMM Vivex, Glass

**RATINGS**

cETLus  
 Wet Location



**ADDITIONAL**

OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER  
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com