



PRODUCT DESCRIPTION

Stately outdoor sconces reference classic lantern shapes and are constructed of Maxim's proprietary Vivex composite, a robust weather-resistant materials guaranteed to withstand harsh weather climates. Available in several sizes and illuminated with clusters of candle sockets, this is a timeless design built to last.

MEASUREMENTS

DIMENSION : 13" W x 24.75" H x 14.5" Ext
 BACK PLATE : 6.5" W x 11.5" H x 6.25" HCO
 HANGING WEIGHT : 5 lb

LAMPING

INPUT VOLTAGE : 120V
 BULB : 3 x 60W Incandescent E12 Candelabra , 180W Total
 BULB INCLUDED : (Not Included)
 DIMMABLE :

FINISHES OPTION

 Black

GLASS

Clear CL

MATERIAL

Vivex, Glass

RATINGS

Wet Location



ADDITIONAL

INSTALL UP/DOWN: Up
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com