



PRODUCT DESCRIPTION

Inspired by classic colonial design, these climate-tough pocket sconces offer traditional charm and stylish finish combinations. Clear glass allows unobstructed light output and visibility into the sconces with candlesticks that stand out in their off-white finish. While the outer frame is made in a textured Black Oxide finish, the interior plate is finished either in a matching finish or contrasting Antique Copper or Verdigris finish. Available as a one, two, or three-light wall sconce, this offering of pocket sconces presents another style of Vivex outdoor products complementing more traditional exteriors.

MEASUREMENTS

DIMENSION : 10.5" W x 22" H x 5" Ext
 BACK PLATE : 13.5" HCO
 HANGING WEIGHT : 19.36 lb

LAMPING

BULB : 3 x 40W Incandescent E12 Candelabra , 120W Total
 BULB INCLUDED : (Not Included)
 DIMMABLE :

FINISHES OPTION

-  Antique Copper / Black Oxide
-  Black Oxide
-  Verdigris / Black Oxide

GLASS

Clear CL

MATERIAL

Vivex, Glass, Aluminum

RATINGS

Wet Location



ADDITIONAL

INSTALL UP/DOWN: Up
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com