



PRODUCT DESCRIPTION

Clean lines and Clear glass form the structure similar to a classic coach lantern. Produced of 304 Grade Stainless Steel and Aluminum, the Rincon set of LED outdoor sconces suit a variety of aesthetics both modern and traditional. Finished in a vibrant two-tone black and gold finish, these sconces are sure to provide updated curb appeal to your exterior.

MEASUREMENTS

DIMENSION : 7" W x 10" H x 4" Ext
 BACK PLATE : 5.5" W x 6.5" H x 5.5" HCO
 HANGING WEIGHT : 2.5 lb

LAMPING

INPUT VOLTAGE : 120V
 LUMENS : 980 Rated (540 Del.)
 BULB : 1 x 14W LED PCB Integrated , 14W Total
 BULB INCLUDED : (Integrated)
 DIMMABLE : Triac Dimmers
 CRI : 90 CRI
 COLOR_TEMP : 3000K

FINISHES OPTION



MATERIAL

Aluminum, Glass, Stainless Steel

RATINGS

cETLus
 Location



ADDITIONAL

RATED LIFE 30000 Hours
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com