




PRODUCT DESCRIPTION

This minimalistic contemporary approach to LED vanity lighting will be the standard for both residential and commercial applications. The light engine features a high quality dimmable driver with multi volt input and high color rendering LEDs for the ultimate vanity lighting.



MEASUREMENTS

DIMENSION : 24" W x 4.75" H x 2.75" Ext
BACK PLATE : 4.75" W x 4.75" H x 2.75" HCO
HANGING WEIGHT : 1.85 lb

LAMPING

INPUT VOLTAGE : 120-277V
LUMENS : 1,440 Rated (1,250 Del.)
BULB : 1 x 16W LED PCB Integrated , 16W Total
BULB INCLUDED : (Integrated)
DIMMABLE : 27-35-40
CRI : 90 CRI
COLOR_TEMP : Select 27/35/40K
LIGHTING_DIRECTION : Omni

FINISHES OPTION

- Black
- Polished Chrome
- Satin Nickel

MATERIAL

Aluminum

RATINGS

cETLus
Damp Location
Energy Star
JA8 ListedADA



ADDITIONAL

INSTALL UP/DOWN: Any
RATED LIFE 45000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746
EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269
P. 626.956.4200 | F. 626.956.4225 | maximlighting.com