



**PRODUCT DESCRIPTION**

Tubular shaped White acrylic diffusers mount to frames of Polished Chrome, Satin Nickel, or Black. Powered by 3000K LED these fixtures work well in a variety of contract applications.

**MEASUREMENTS**

DIMENSION : 48" W x 4.75" H x 2.5" Ext  
 BACK PLATE : 4.75" W x 4.75" H x 2.25" HCO  
 HANGING WEIGHT : 3.75 lb

**LAMPING**

INPUT VOLTAGE : 120V  
 LUMENS : 2,480 Rated (2,240 Del.)  
 BULB : 1 x 32W LED LED , 32W Total  
 BULB INCLUDED : (Integrated)  
 DIMMABLE : ELV or Triac CL  
 CRI : 90 CRI  
 COLOR\_TEMP : 3000K

**FINISHES OPTION**



**MATERIAL**

Aluminum, Acrylic

**RATINGS**

cETLus  
 Damp Location  
 Energy Star  
 JA8 ListedADA



**ADDITIONAL**

INSTALL UP/DOWN: Any  
 RATED LIFE 50000 Hours  
 OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER  
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com