



PRODUCT DESCRIPTION

With solid Die-Cast Aluminum construction and powered by a range voltage input driver, Pathfinder is a high performance down light for commercial and residential installations. Choose from triangular or spherical profiles as they discreetly extend from the wall. Available with a photocell option, these archetypal forms purposely blend into the architectural landscape creating safer spaces that shine light on locations of interest. Available in Black, Architectural Bronze, or Metallic Silver

MEASUREMENTS

DIMENSION : 7" W x 4.5" H x 3.5" Ext
 BACK PLATE : 2.25" HCO
 HANGING WEIGHT : 1.51 lb

LAMPING

INPUT VOLTAGE : 120-277V
 LUMENS : 880 Rated (820 Del.)
 BULB : 1 x 15W LED PCB Integrated , 15W Total
 BULB INCLUDED : (Integrated)
 DIMMABLE : Only at 120V with ELV
 CRI : 80 CRI
 COLOR_TEMP : 3000K
 LIGHTING_DIRECTION : Down

FINISHES OPTION

-  Black
-  Bronze
-  Silver

MATERIAL

Aluminum +Acrylic

RATINGS

cETLus
 Wet Location
 For OutdoorADA



ADDITIONAL

INSTALL UP/DOWN: Down
 PHOTOCELL
 RATED LIFE 50000 Hours
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746
 EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269
 P. 626.956.4200 | F. 626.956.4225 | maxilighting.com