



**PRODUCT DESCRIPTION**


With solid Die-Cast Aluminum construction and powered by a range voltage input driver, Pathfinder is a high performance down light for commercial and residential installations. Choose from triangular or spherical profiles as they discreetly extend from the wall. Available with a photocell option, these archetypal forms purposely blend into the architectural landscape creating safer spaces that shine light on locations of interest. Available in Black, Architectural Bronze, or Metallic Silver

**MEASUREMENTS**

DIMENSION : 7" W x 4.5" H x 3.5" Ext  
 BACK PLATE : 2.25" HCO  
 HANGING WEIGHT : 1.4 lb

**LAMPING**

INPUT VOLTAGE : 120-277V  
 LUMENS : 880 Rated (820 Del.)  
 BULB : 1 x 15W LED PCB Integrated , 15W Total  
 BULB INCLUDED : (Integrated)  
 DIMMABLE : Only at 120V with ELV  
 CRI : 80 CRI  
 COLOR\_TEMP : 3000K  
 LIGHTING\_DIRECTION : Down



**FINISHES OPTION**

-  Architectural Bronze
-  Black
-  Silver

**MATERIAL**

Aluminum +Acrylic

**RATINGS**

cETLus  
 Wet Location  
 For OutdoorADA



**ADDITIONAL**

INSTALL UP/DOWN: Down  
 RATED LIFE 50000 Hours  
 OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

PHOTOMETRIC: Report Found Online

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER  
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com