



PRODUCT DESCRIPTION

Referencing the classic French-styled roof line, the Mansard LED sconces accentuate the volume of the roof shape in a more traditional styling than other simpler geometries. High powered LED lights are recessed within these sconces to conceal the light source and provide a Dark Sky application for light directing it downwards alone.

MEASUREMENTS

DIMENSION : 6.5" W x 6.25" H x 6.5" Ext
 BACK PLATE : 4.75" W x 6.25" H x 3.25" HCO
 HANGING WEIGHT : 2.2 lb

LAMPING

INPUT VOLTAGE : 120V
 LUMENS : 750 Rated (450 Del.)
 BULB : 1 x 12W LED AC Integrated , 12W Total
 BULB INCLUDED : (Integrated)
 CRI : 90 CRI
 COLOR_TEMP : 3000K
 LIGHTING_DIRECTION : Down

FINISHES OPTION

-  Antique Brass
-  Black

MATERIAL

Aluminum

RATINGS

Wet Location



ADDITIONAL

INSTALL UP/DOWN: Down
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com