




PRODUCT DESCRIPTION

Tubular shaped White acrylic diffusers mount to frames of Polished Chrome, Satin Nickel, or Black. Powered by 3000K LED these fixtures work well in a variety of contract applications.



MEASUREMENTS

DIMENSION : 24" W x 4.75" H x 2.75" Ext
 BACK PLATE : 4.75" W x 4.75" H x 2.75" HCO
 HANGING WEIGHT : 2.02 lb

LAMPING

INPUT VOLTAGE : 120V
 LUMENS : 1,600 Rated (1,400 Del.)
 BULB : 1 x 16W LED AC Integrated , 12W Total
 BULB INCLUDED : (Integrated)
 DIMMABLE : 27-35-40
 CRI : 90 CRI
 COLOR_TEMP : Select 27/35/40K
 LIGHTING_DIRECTION : Omni

FINISHES OPTION

-  Black
-  Satin Nickel

MATERIAL

Aluminum

RATINGS

cETLus
 Damp Location
 Energy Star
 JA8 ListedADA



ADDITIONAL

INSTALL UP/DOWN: Any
 RATED LIFE 35000 Hours
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com