



PRODUCT DESCRIPTION

This very compact LED flush mount directly installs on any 4" junction box and gives the look of a recessed trim. Constructed of Die Cast Aluminum, the Diverse luminaire is dimmable and also approved for wet or damp locations so it can be used in virtually any ceiling application, including showers.

MEASUREMENTS

DIMENSION : 6" L x 6" W x 1.25" H
 HANGING WEIGHT : 0.29 lb

LAMPING

INPUT VOLTAGE : 120V
 LUMENS : 800 Rated (750 Del.)
 BULB : 1 x 11W LED PCB Integrated , 11W Total
 BULB INCLUDED : (Integrated)
 DIMMABLE : Triac/ELV dimming
 CRI : 90 CRI
 COLOR_TEMP : 4000K
 LIGHTING_DIRECTION : Down

FINISHES OPTION

 White

GLASS

White WT

MATERIAL

Aluminum + PC

RATINGS

cETLus
 Wet Location
 Energy Star
 CA Title 24
 ADA



ADDITIONAL

INSTALL UP/DOWN: UP
 RATED LIFE 50000 Hours
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746
 EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269
 P. 626.956.4200 | F. 626.956.4225 | maximlighting.com