



PRODUCT DESCRIPTION

MEASUREMENTS

DIMENSION : 10" L x 10" W x 0.5" H
HANGING WEIGHT : 1.75 lb

LAMPING

INPUT VOLTAGE : 120-277V
LUMENS : 1,200 Rated (1,200 Del.)
BULB : 1 x 20W LED PCB Integrated , 20W Total
BULB INCLUDED : (Integrated)
DIMMABLE : 0-10V
CRI : 90+ CRI
COLOR_TEMP : 3000K

FINISHES OPTION

 Satin Nickel

GLASS

White WT

MATERIAL

PMMA Acrylic, Aluminum

RATINGS

cETLus
Wet Location
Energy Star
JA8 ListedADA



ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

PHOTOMETRIC: Report Found Online

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maxilighting.com