



PRODUCT DESCRIPTION

This very compact LED flush mount directly installs on any 4" junction box and gives the look of a recessed trim. Constructed of Die Cast Aluminum, the Diverse luminaire is dimmable and also approved for wet or damp locations so it can be used in virtually any ceiling application, including showers.

MEASUREMENTS

DIMENSION : 13" L x 13" W x 1.75" H
 HANGING WEIGHT : 1.78 lb

LAMPING

INPUT VOLTAGE : 120V
 LUMENS : 2,250 Rated (1,750 Del.)
 BULB : 1 x 24W LED PCB Integrated , 25W Total
 BULB INCLUDED : (Integrated)
 DIMMABLE : ELV or Triac CL
 CRI : 90 CRI
 COLOR_TEMP : 3000K
 LIGHTING_DIRECTION : Down

FINISHES OPTION

 Satin Nickel
 White

GLASS

White WT

MATERIAL

Polycarbonate, Steel

RATINGS

cETLus
 Wet Location
 Energy Star
 JA8 ListedADA



ADDITIONAL

INSTALL UP/DOWN: UP
 RATED LIFE 50000 Hours
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com