

**PRODUCT DESCRIPTION**

A trendy two-tone Black and Gold low-profile flush mount to coordinate with the ever popular two-tone product designs throughout your project. The slim profile and stylish finish make this LED flush mount a dapper choice to pair with other Black and Gold furniture, furnishings, and plumbing options available. Available in two diameters 12" and 16" that house powerful LED light sources.

MEASUREMENTS

DIMENSION : 12" L x 12" W x 2" H
HANGING WEIGHT : 3.19 lb

LAMPING

INPUT VOLTAGE : 120V
LUMENS : 1,800 Rated (1,360 Del.)
BULB : 1 x 20W LED AC Integrated , 20W Total
BULB INCLUDED : (Integrated)
DIMMABLE : Triac
CRI : 90 CRI
COLOR_TEMP : 3000K
LIGHTING_DIRECTION : Down

FINISHES OPTION

 Black / Antique Brass

GLASS

White WT

MATERIAL

Steel

RATINGS

cETLus
Damp Location
CA Title 24

**ADDITIONAL**

INSTALL UP/DOWN: UP
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com