

**PRODUCT DESCRIPTION****MEASUREMENTS**

DIMENSION : 8.5" W x 12.25" H x 10.5" Ext  
MAX OAH : 4.5" W x 5" H  
HANGING WEIGHT : 2.05 lb

**LAMPING**

INPUT VOLTAGE : 120V  
LUMENS : 685 Rated  
BULB : 2 x 10W LED GU24 + PCB , 10W Total  
BULB INCLUDED : (Included)  
DIMMABLE : No  
CRI : 80+ CRI  
COLOR\_TEMP : 3000K

**MATERIAL**

Steel, Fabric Shade

**ADDITIONAL**

INSTALL UP/DOWN: Up  
OPERATING TEMPERATURE:  
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



**WESTERN DISTRIBUTION CENTER (HEADQUARTER)**  
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

**EASTERN DISTRIBUTION CENTER**  
4200 SHIRLEY DR. | ATLANTA, GA 30336

P. 626.956.4200 | F. 626.956.4225 | [maximlighting.com](http://maximlighting.com)