



#### PRODUCT DESCRIPTION

An Articulating Dome or Cylinder mono point Wall Sconce featuring sleek, streamlined design and directional shade that provides focused directed light. Available in Naturally Aged Brass and Matte Black outdoor rated powder coats and constructed of non-corrosive aluminum, this straight or dome-shaped shade is a stylish alternative to security flood lighting with interior appeal as a bedside or reading sconce.

#### MEASUREMENTS

DIMENSION : 3.75" W x 6.5" H x 6.25" Ext  
 BACK PLATE : 4.75" W x 4.75" H x 2.38" HCO  
 HANGING WEIGHT : 1.21 lb

#### LAMPING

INPUT VOLTAGE : 120V  
 LUMENS : 800 Rated (600 Del.)  
 BULB : 1 x 9W LED E26 Medium , 9W Total  
 BULB INCLUDED : (Integrated)  
 CRI : 90 CRI  
 COLOR\_TEMP : 3000K  
 LIGHTING\_DIRECTION : Directional

#### FINISHES OPTION

 Black  
 Natural Aged Brass

#### MATERIAL

Aluminum

#### RATINGS

Damp Location  
 JA8 Bulb In



#### ADDITIONAL

INSTALL UP/DOWN: Down  
 OPERATING TEMPERATURE:  
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)  
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER  
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com