



PRODUCT DESCRIPTION

An Articulating Dome or Cylinder mono point Wall Sconce featuring sleek, streamlined design and directional shade that provides focused directed light. Available in Naturally Aged Brass and Matte Black outdoor rated powder coats and constructed of non-corrosive aluminum, this straight or dome-shaped shade is a stylish alternative to security flood lighting with interior appeal as a bedside or reading sconce.

MEASUREMENTS

DIMENSION : 3.75" W x 6.5" H x 6.25" Ext
 BACK PLATE : 4.75" W x 4.75" H x 2.38" HCO
 HANGING WEIGHT : 1.1 lb

LAMPING

INPUT VOLTAGE : 120V
 LUMENS : 800 Rated (600 Del.)
 BULB : 1 x 9W LED E26 Medium , 9W Total
 BULB INCLUDED : (Included)
 DIMMABLE :
 CRI : 90 CRI
 COLOR_TEMP : 3000K
 LIGHTING_DIRECTION : Directional

FINISHES OPTION

 Black
 Natural Aged Brass

MATERIAL

Aluminum

RATINGS

Damp Location
 JA8 Bulb In



ADDITIONAL

INSTALL UP/DOWN: Down
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com