



PRODUCT DESCRIPTION

Sweeping arcs define this fan, designed for contemporary and refreshing upgrades. The central housing is domical, from which a trio of uniquely curved fan blades smoothly rotate. Available in Satin Nickel with Silver blades and Black with two-tone Walnut/Black blades, the Cupola also features an LED integrated dome shape or a 2 lamp light kit with a domical glass to create a perfect sphere.

MEASUREMENTS

DIMENSION : 52" L x 52" W x 14.25" H
 MAX OAH : 5.75" W x 22.75" H
 CANOPY : 5.25" W x 2.25" H
 HANGING WEIGHT : 17.28 lb

LAMPING

INPUT VOLTAGE : 120V
 LUMENS : 2,100 Rated (1,680 Del.)
 BULB : 1 x 24W LED PCB Intergarad , 24W Total
 BULB INCLUDED : (Integrated)
 DIMMABLE : Y
 CRI : 90 CRI
 COLOR_TEMP : 3000K

FINISHES OPTION

 Black
 Oil Rubbed Bronze
 Satin Nickel

MATERIAL

Metal + ABS + PC

RATINGS

cETLus
 Dry Location



ADDITIONAL

RATED LIFE 40000 Hours
 OPERATING TEMPERATURE:
 -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
 253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
 101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com