

**PRODUCT DESCRIPTION**

An innovative, slim channel LED light bar. The 120V input Slim Stick connects to a slim direct wire installation junction box where brightness and white color tunable LED light can be adjusted with the touch of a button. The control is the first in the industry to provide color temperature control variable between 2700-5000k on a driverless 120V LED strip. Included with the product, mounting clips allow the user install the channels flat or at an angle up to 90 degrees, so the product can be used in more applications such as cove, task, and closet lighting.

MEASUREMENTS

DIMENSION : 12" L x 3.5" W x 1" H
HANGING WEIGHT : 0.99 lb

LAMPING

INPUT VOLTAGE : V
BULB :

FINISHES OPTION

 Black
 White

RATINGS

cETLus
Dry Location

**ADDITIONAL**

OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com