



## PIG™ Microbial Oil Remediator for Soil, Grass and Water

CLN935 Remediator, (2) 2.5 gal. Container, 2 per box

Break down and eliminate oil and fuel on soil, grass and water with our stormwater-safe solution. Environmentally friendly formula requires no containment or cleanup!

- Gradually remove oil and fuel from soil, grass and water to eliminate rain runoff
- BioBreaker microbes digest hydrocarbons through bioremediation, naturally converting them into water and harmless gases
- Stormwater-safe solution can enter storm drains without harming the environment
- Easier than using cleaners and degreasers that cannot be allowed into waterways or groundwater systems — just check the SDS, Section 6, on competitor cleaners to see the warning!
- Applies easily using a manual sprayer; product is designed to work over time as a repeated application
- Product is concentrated and must be diluted 10:1; each diluted gallon will remediate approximately one cubic yard of soil or 200 gallons of water



### Specifications

Style	Remediator
Brand	PIG
Intended Use	Soil and Water
Temperature Limit	Works from 42°F ( 5.5°C) to 120°F (49°C)
Treats	Treats 10,000 gal. or up to 50 cu. yds.
Volume	(2) 2.5 gal. Container
Color	Green
VOC Content	VOC-Free
Sold as	2 per box
Weight	46 lbs.
# per Pallet	36

## Composition

Water 89%  
Alkypolyglycoside 6%  
Bacterial Cultures 5%  
Green Dye

## Shelf Life

2 years

## UNSPSC

47131821

## Metric Equivalent

## Weight

20.9 kg

## Technical Information

### US Only

This product can ONLY be shipped to the United States.

## Technical Documents

[Technical Data Sheet for PIG® Microbial Oil Remediator for Soil, Grass and Water](#)



**One Pork Avenue • Tipton, PA 16684-0304**

1-855-493-4647 • Fax: 1-800-621-7447 • [newpig.com](http://newpig.com) • [hothogs@newpig.com](mailto:hothogs@newpig.com)