

Grip Tight™ Circuit Breaker Lockout

LCK240 Circuit Breaker Lockout, For 120V Breakers and 240V Breakers, 1 each

Secure breaker toggles to improve safety and help meet lockout/tagout (LOTO) regulations.

- Securely disables electrical shut-offs by putting breaker toggles under lock and key
- Grip Tight design provides superior hold strength; thumb turn and clamp handle offer a custom, secure fit
- Slim profile allows side-by-side toggle lockout
- Durable powder-coated steel and reinforced polymer construction allow use in harsh environments
- Installs easily to instantly safeguard machinery and equipment
- Accepts one padlock or hasp (not included)
- This simple lockout/tagout solution will help your facility meet life-saving regulations
- Fits toggles that are standard on 120V breakers, as well as tie-bar toggles on 240V breakers



Master Lock.

Specifications

Use With	120V Breakers and 240V Breakers
Brand	Master Lock
Lockout Style	Circuit Breaker Lockout
Temperature Limit	-50°F (-46°C) to 360°F (183°C)
Sold as	1 each
Weight	1 lb.
Color	Red
Composition	Steel, Polymer
UNSPSC	46171511

Metric Equivalent

Weight	.5 kg
--------	-------

Technical Information

Technical Documents

29 CFR 1910.147

