



Safety Data Sheet

1. Product And Company Identification

Product Identifier: PIG Grippy® Floor Mat (MSD-195)

General Use: PIG Grippy® Floor Mats are designed to stay in place to prevent them from sliding around or becoming a trip hazard. The poly backing will keep liquids from reaching the floor while keeping any leaks and drips on the mat. The Grippy® Floor Mat holds up to foot and wheeled traffic as well as heavy equipment such as forklifts. Grippy® Floor Mat absorbs non-aggressive liquids such as oil, water, solvents and coolants.

Product Description: Black, gray or tan adhesive-backed absorbent mat with needle punched stitching, used in high traffic areas.

Specific Product Identifier: PIG Grippy®: Leak & Drip Mat, Leak & Drip Pads, Floor Mat, Restroom Mat, No Trip Commercial Mat and TRAFFIC MAT® Rug.

COMPANY PROFILE: **EMERGENCY TELEPHONE:**

New Pig Corporation
One Pork Avenue
Tipton, PA 16684-0304
Information Number
1-800-468-4647

INFOTRAC
200 North Palmetto Street
Leesburg, FL 34748
24 hrs, 7 days/week
1-800-535-5053

Website: www.newpig.com, **Email:** hothogs@newpig.com

2. Hazards Identification

GHS Classification: Not a dangerous substance according to GHS

POTENTIAL HEALTH EFFECTS:

Eye Contact: No hazard in normal use of product

Ingestion: No hazard in normal use of product

Inhalation: No hazard in normal use of product

Skin Contact: Not applicable

Chronic: Not applicable

3. Composition/Information on Ingredients

CAS: 9003-07-0 Polypropylene >97%

Minor Additives:

CAS: 1333-86-4 Carbon black* <1%

EC: 215-609-9

CAS: Mixture Adhesive

CAS: 9002-88-4 Polyethylene film

May contain:

Proprietary Anti-microbial agent <0.01%

CAS: Mixture Blue, yellow, red, white, black ink

*In its present form, carbon black is completely bound in the mat, so there is little or no dust to present an airborne hazard

4. First Aid Measures

Eye Contact: Not applicable

4. First Aid Measures (Cont'd)

Ingestion: Not applicable

Inhalation: Not applicable

Skin Contact: Not applicable

5. Fire Fighting Measures

Extinguishing Media: Unused form: Not applicable Used form: that which is compatible to liquid(s) absorbed.

Special Fire Fighting Procedures: Wear a self-contained breathing apparatus and refer to absorbed liquid(s) SDS(s).

Hazardous Combustion Products: When heated above the melting point: carbon monoxide, carbon dioxide, acrolein, ketones, aldehydes and other unidentified organic compounds.

Unusual Hazards: Refer to absorbed liquid(s) SDS(s). The PIG Grippy® Floor Mats do not render liquids nonflammable, neutral or less hazardous.

6. Accidental Release Measures

Spill or Leak Procedures: If material is unused, sweep or pick up and dispose of as a non-hazardous material.

7. Handling and Storage

Handling Precautions: None

Storage Precautions: Store in a cool, dry place. **Shelf Life:** Indefinitely - as long as product is kept in a clean, dry place away from direct sunlight.

General: Refer to absorbed liquid(s) SDS(s). The container can be hazardous when empty. Follow label cautions even after the container is empty. Do not re-use empty containers for food, clothing or products for human or animal consumption, or where skin contact can occur.

8. Exposure Controls/Personal Protection

Engineering Controls: None required

PERSONAL PROTECTION

Eyes: Safety glasses with side shields is a good industrial practice

Respirator: Not required.

Gloves: Not normally required. However, use of cloth, canvas or leather gloves is a good industrial practice.

Other: None required.

OSHA HAZARDOUS COMPONENTS (29 CFR 1910.1200):

EXPOSURE LIMITS 8 hrs. TWA (ppm)

OSHA PEL

ACGIH TLV

Carbon Black

3.5 mg/m³

3.0 mg/m³ (inh)

In its present form, there is little or no dust to present an OSHA hazard



Safety Data Sheet

9. Physical and Chemical Properties

Appearance: Black, gray or tan mat with adhesive backing.
Odor: No odor **Odor Threshold:** Not applicable
pH: Not applicable
MELTING POINT/Freezing Point: >320° F (>160° C)
Initial Boiling Point and Range: Not applicable
Flash Point: Not applicable **Method:** Not applicable
Evaporation Rate: Not applicable
Flammable Limits: Not applicable
Conditions of Flammability: Not established
Explosive Properties: Not applicable
Vapor Pressure: Not applicable
Vapor Density: Not applicable
Relative Density (H₂O = 1): 0.9
Solubility in Water: Insoluble
Auto Ignition Temperature: >675° F (>357° C)
Coefficient of Water/Oil Distribution: Not available

10. Stability and Reactivity

General: This is a stable material.
Conditions of Reactivity: Not established
Incompatible Materials: Strong oxidizing agents may degrade product over an extended period of time.
Conditions to Avoid: Not applicable
Hazardous Decomposition: When heated, it may emit toxic fumes.
Hazardous Polymerization: Will not occur

11. Toxicological Information

In its present form, carbon black is completely bound in the mat, so there is little or no dust to present an airborne hazard

LD50: Not available. Carbon black: LD50 Oral Rat >8000 mg/kg
LC50: Not available

Carcinogenicity: IARC: Carbon black, Group 2B
National Toxicology Program: Not listed
OSHA: See Section 15
California Prop 65: No listed ingredient

Reproduction Toxicity: Not available
Teratogenicity: Not available
Mutagenicity: Not available
Synergistic Products: Not available
Irritancy of Product: See Section 2.
Sensitization to Product: Not available

12. Ecological Information

No data available

13. Disposal Considerations

Waste Disposal Method: If unused, no special precautions are necessary. Dispose of in accordance with federal, state and local regulations. In certain types of cleanup applications, the nature of the material recovered will classify the resulting spent material as a hazardous component. In such instances the material should be disposed of via an approved hazardous waste disposal service and the appropriate manifesting obtained.

14. Transport Information

DOT (Department of Transportation):
Proper Shipping Name: Not regulated
Hazard Class: Not regulated
Identification Number: Not applicable

15. Regulatory Information

CERCLA (Comprehensive Environmental Response Compensation and Liability Act): No Reportable Quantity
OSHA Hazard Communication Standard, 29 CFR 1910.1200: Carbon Black <1%
SARA Title III (Superfund Amendments and Reauthorization Act): No listed ingredient
TSCA (Toxic Substances Control Act): Ingredients of this product are on the Inventory list.
DSL (Canadian Domestic Substances List): All components of this product are on the Canadian DSL.

16. Other Information

Reason for Issue: Reviewed, changes to Sections 15 & 16.
Prepared by: Dale Gatehouse, Entreprises Krenda Inc.
Approved by: Lisa Baxter, New Pig Corporation
Previous Date of Issue: 05/06/2020
Revised Date: 04/30/2021
SDS Number: MSD-195

The following is in lieu of all warranties, expressed or implied: All information provided is based on testing and data believed to be accurate.